





- Do not use the forearm-protection close to moving machine parts.
- Check the gloves carefully before use to make certain there are no defects or imperfections.
- It is reasonable to assume that the forearm-protection also protect against sharp objects such as injection needles, provided they satisfy the requirements of perforation resistance according to EN 388:2016+A1:2018.
- Discard damaged, worn, dirty or soiled forearm-protection, irrespective of the substance (including on the inside), as they may lead to skin irritation and rashes. Consult a doctor or dermatologist should such cases arise.

## EN ISO 21420:2020 - Protective gloves - General requirements and test methods:

This standard specifies the relevant test methods to be used for all protective gloves and the general requirements for design principles, glove assembly, resistance of the glove material to water penetration, harmlessness, comfort and performance as well as the labeling to be carried out by the manufacturer and the information to be provided by the manufacturer.

## EN 388:2016+A1:2018 - Protective gloves against mechanical risks:

Protective gloves against mechanical risks must achieve at least Level 1 or Level A in at least one of the properties (abrasion, cut, tear and puncture resistance) of the TDM cut resistance test according to EN ISO 13997:1999.

Abrasion resistance:	The number of abrasion cycles required to rub through the test specimen.
Cut resistance (Coupe-Test):	The number of test cycles in which the test specimen is cut through with constant force and repeated contact.
Tear resistance:	The force needed to continue tearing the cut sample.
Puncture resistance:	The force needed to puncture the sample using a standardized test stylus.
Cut resistance (TDM):	The minimum force that is necessary to cut through the test specimen with a single contact.

### EN 388:2016+A1:2018



2X4XC

Test criteria	Rating	Article 2613
A = Abrasion resistance	0 - 4	2
B = Cut resistance (Coupe test)	0 - 5	X
C = Tear resistance	0 - 4	4
D = Puncture resistance	0 - 4	X
E = Cut resistance (TDM) according to EN ISO 13997:1999	A - F	C
F = Impact protection test according to EN 13594:2015	P	X

The higher the test number, the better the test performance. X means 'not tested'. P means 'passed'.

Test	1	2	3	4	5
A = Abrasion resistance (number of abrasion cycles)	100	500	2000	8000	-
B = Cut resistance (index) Coupe test	1,2	2,5	5,0	10,0	20,0
C = Tear resistance (N)	10	25	50	75	-
D = Puncture resistance (N)	20	60	100	150	-

Test	A	B	C	D	E	F
E = Cut resistance according to EN ISO 13997:1999 (N)	2	5	10	15	22	30
Article 2613						

## EN 13594:2015 - Impact protection:

Every area specified as providing protection against impact must be tested. The test method (dimensions of the test sample) does not permit impact testing of the finger protection. Gloves to protect against mechanical risks may be designed and manufactured in such a way that they offer specific impact damping (e.g. impact protection on the knuckles, the back of the hand, the palms). These gloves must satisfy the requirements of Level 1 according to EN 13594:2015.

The results of the Coupe test must only be taken as indications if blunting occurs during the cut resistance test (B), while the TDM cut resistance test (E) provides reference results in regard to performance.

## Markings on the arm sleeves:

Trademark, art.-no. of manufacturer, size, CE-icon, pictograms with the corresponding numbers of the relevant European PPE standards, i-mark, factory icon with date of manufacture: month/year, hourglass pictogram with expiry date: month/year



HANDSCHUHE >>

teXXor

2613

10



Brand label of manufacturer

Article no. of the manufacturer

Size of arm protectors according to EN ISO 21420:2020 (example)

The CE marking confirms compliance with the requirements of European Regulation 2016/425.

i mark: Reference to the manufacturer's information.

Pictograms with the corresponding numbers of the relevant European PPE standards (example, detailed pictogram see previous pages).

Date of manufacture month/year: 00/0000

Expiry date month/year: 00/0000

#### Dimensions/weights article:

Size	Length in cm	Width in cm	material thickness palm i	Weight in g/pair
8	41		0,09	
10	41		0,09	
12	41		0,09	

The above values are approximate and subject to slight variations.

#### Details of packaging unit:

Size	kg gross	kg net	Length in cm	Width in cm	Height in cm
8					
10					
12					

The above values are approximate and subject to slight variations.

#### Hazardous ingredients - REACH (Registration, Evaluation, Authorization and Restriction of Chemicals):

The product is manufactured in compliance with Annex XVII of the European REACH regulation 1907/2006 and contains no hazardous substances in concentrations requiring declaration.

#### Declaration of Conformity

CE These products are classified as personal protective equipment (PPE). The CE mark confirms that the product satisfies the applicable requirements of Regulation (EU) 2016/425.

#### Identification and selection:

**Selection of model must be made according to workplace requirements, type of hazard and relevant environmental conditions. The employer is responsible for choosing the right PSA. Therefore, it is necessary to check the suitability of the product for the needs needed before use.**

#### Regulation for use:

The product fulfils the safety requirements only if they are worn in an entirely correct manner and in their best condition. Check the product for defects or flaws before use. If any tears or holes appear during use of the product, they must be disposed of immediately. Make sure that the product are not too large or too small and fit exactly. Modifications to this PPE are not permitted. Follow the instructions provided in the manufacturer's information and keep this information in a safe place during the entire service life of the PPE. We assume no responsibility for any damages and/or consequences resulting from improper use.

#### Care instructions:



Do not wash and bleach the arm protection. Drying in tumbler is not possible. Do not iron. Professional dry and wet cleaning is not allowed.



HANDSCHUHE >>

#### Storage and aging:

The product should be stored in their original packaging in a dark, cool and dry place, away from direct sunlight and away from any sources of heat. Prolonged contact with direct sunlight or excessive heat will shorten the service life. Avoid any contact of the product with solvents which could result in changes to the product or its properties. The service life is generally up to 5 years when used and stored properly (see also expiry date on the packaging). The product are also marked with the production date (month/year).

#### Disposal:

Used products may be contaminated with environmentally harmful or hazardous substances. Dispose of in accordance with applicable local laws.

#### Health risks:

Allergies, caused by the proper use of the products, are not yet known. If an allergic reaction still occurs, consult a doctor or dermatologist.

#### First Aid:

Remove the product if they are contaminated with hazardous materials.

In case of contact with skin: immediately consult a doctor if an allergic reaction occurs.

In case of eye contact: wash out the affected eye with water. Consult a doctor immediately.

#### The notified body responsible for the EU Type Examination:

ZVD Zavod za varstvo pri delu d.o.o.

Chengdujska cesta 25

1260 Ljubljana-Polje

Slovenia

Notified Body No.: 1493

**For the full Declaration of Conformity and manufacturer's information, please visit:**

[www.big-arbeitsschutz.de](http://www.big-arbeitsschutz.de)



issued on 26.01.2024/Rev.01